

# Romex® SIMpull® Type NM-B

Nonmetallic-Sheathed Cable. 600 Volt.  
Copper Conductors. Color-Coded Jacket.  
Four Conductor Available With Two Neutrals.  
SIM Jacket® Designed for Easier Pulling.



## APPLICATIONS

Southwire's Romex SIMpull Type NM-B (nonmetallic-sheathed cable) may be used for both exposed and concealed work in normally dry locations at temperatures not to exceed 90°C (with ampacity limited to that for 60°C conductors) as specified in the 2011 National Electrical Code. NM-B cable is primarily used in residential wiring as branch circuits for outlets, switches, and other loads. NM-B cable may be run in air voids of masonry block or tile walls where such walls are not wet or damp locations. Voltage rating for NM-B cable is 600 volts.

## SPECIFICATIONS

Southwire's Romex SIMpull Type NM-B cable complies with:

- ASTM B-3 and B-8
- UL Standard 83
- UL Standard 719
- Federal Specification A-A-59544
- National Electrical Code, NFPA 70. 2011 Edition
- RoHS/ REACH

## CONSTRUCTION

Southwire's Romex SIMpull Type NM-B cable is manufactured as 2, 3, or 4 conductor cable, with a bare ground wire. Copper conductors are annealed (soft) copper. Stranded conductors are compressed stranded. Conductor insulation is 90°C-rated polyvinyl chloride (PVC), nylon jacketed. Southwire's Romex SIMpull Type NM-B is designed for Easier Pulling, Resulting in Easier installation. The cable jacket is color-coded for quick size identification; White - 14 AWG, Yellow - 12 AWG, Orange - 10 AWG, and Black - 8 AWG and 6 AWG.

# CU-NM-B

Conductor				Ground Wire		Approx. Cable Dimension (mils)	Approx. Net Weight per 1000' (lbs)	Allowable Ampacity+	Standard Package
Size (AWG)	Number of Conductors	Number of Strands	Insulation Thickness (mils)	Size (AWG)	Number of Strands				
<b>TWO CONDUCTOR</b>									
14	2	1	19	14	1	360X162	57	15	BEF
12	2	1	19	12	1	410X179	82	20	BEF
10	2	1	24	10	1	494X210	124	30	ABE
8	2	7	35	10	1	612X269	186	40	ABCD
6	2	7	35	10	1	683X304	225	55	BDF
<b>THREE CONDUCTOR</b>									
14	3	1	19	14	1	307	74	15	BDF
12	3	1	19	12	1	347	107	20	BE
10	3	1	24	10	1	422	164	30	BCE
8	3	7	35	10	1	565	253	40	ABCD
6	3	7	35	10	1	650	357	55	ABCD
4	3	7	46	8	1	814	560	70	BCD
2	3	7	46	8	1	952	816	95	BCD
<b>FOUR CONDUCTOR</b>									
14	2/2	1*	19	14	1	336	91	15	BE
14	4	1**	19	14	1	336	91	15	BE
12	2/2	1*	19	12	1	381	132	20	BE
12	4	1**	19	12	1	381	132	20	BE
10	4	1	24	10	1	465	201	30	BE
+ Ampacities per National Electrical Code section 310.15 and 334.80, 2011 Edition NOTE: Jacket thickness for all NM-B cable is 30 mils * Color code for 2/2 conductor cable is Black, White, Red and White with Red stripe. ** Color code for 4 conductor cable is Black, White, Red and Blue.								<b>PACKAGE CODE:</b> A - 2500' Reel B - 1000' Reel C - 500' Spool D - 125' Coil E - 250' Coil F - 500' Coil	

## RECOMMENDED SAMPLE SPECIFICATIONS:

Conductors shall be UL-listed Type NM-B, suitable for operation at 600 volts in all installations as specified in the National Electrical Code. SIMpull<sup>®</sup> jacketed conductors shall be annealed copper as manufactured by Southwire Company or approved equal.



Copyright 2010, Southwire Company. All Rights Reserved.  
 ®Southwire is a registered trademark of Southwire Company.